


# Product Data Sheet

| Part no. | Name                                          | Type         |
|----------|-----------------------------------------------|--------------|
| 1384933  | INKO Module Base Unit INKO-M BU 40 Polypropyl | INKO-M BU 40 |



**Description:** Clamp Halves for the INKO® Module Clamp system.



**Additional information:** For Module base units from 21 to 42 mm tubing: Place a Base Plate and then the first half part of the tubing clamp into the steel module base before placing the tube. Add the second half part and a Top Pressure Plate before fixing with the Lock Plate. To add an additional level to the module: Release the Lock Plate and remove the Pressure Plate on top of the clamp halves surrounding the tubing. Place a single bolted module base where the Pressure Plate was and retighten using the Lock Plate.

## Characteristics

| Name             | Value |
|------------------|-------|
| Weight (kg)      | 0.01  |
| X (mm)           | 24.9  |
| Y (mm)           | 57    |
| Z (mm)           | 46    |
| D1 Diameter (mm) | 40    |
| Torque (Nm)      | 16    |
| Tubing Size (mm) | 40    |



Product images are a general representation of the product design however some variances may occur.

## Product packaging information

|                   |                     |                                                                                                          |
|-------------------|---------------------|----------------------------------------------------------------------------------------------------------|
| <b>F-PAK GTIN</b> | <b>Single piece</b> | <br>7 070693 849333 |
| <b>D-PAK GTIN</b> |                     |                                                                                                          |